

TESTED TO BE TOUGH STUFF

YOUR LEAD-FREE/COST COMPETITIVE SOLUTION



CORROSION, THERMAL EXPANSION AND HEAT GENERATION

ECO BRONZE™ has been independently tested and proven to be a superb lead-free, environmentally friendly alternative to the standard C93200 leaded tin bronze alloy.

It was put through a variety of tests at independent laboratories for bearing alloy attributes, including dezincification to prove its resistance.



CORROSION

Dezincification is the selective leaching of zinc from brass. It is important that the bearing alloy chosen is resistant to this phenomenon.

TEST: ECO BRONZE and other common bearing alloys were tested for dezincification resistance per the ISO 6509 protocol., and for added severity, the test was extended from 24 hours to 144 hours.

ECO BRONZE showed the same resistance even in the longer test.

RESULTS: ECO BRONZE was among the leaders with ZERO dezincification

ISO 6509 DEZINCIFICATION TESTING COMPARISON

| Alloy | Commercial | Dezincification | Cu% | Zn% | Pb% | Sn% | Si% | S% | P% |
|--------|----------------------|-----------------|-----|-----|-----|-----|-----|-----|-----|
| C83470 | Biwalite | 0 | 93 | 2 | | 4 | | 0.4 | |
| C83600 | 85 Metal | 0 | 85 | 5 | 5 | 5 | | | |
| C87850 | ECO BRONZE | 0 | 76 | 21 | | | 3 | | 0.1 |
| C90300 | Tin Bronze | 0 | 88 | 4 | 8 | | | | |
| C93200 | High Lead Tin Bronze | 0 | 83 | 3 | 7 | 7 | | | |
| C93700 | Bearing Bronze | 0 | 80 | 10 | 10 | | | | |

ECO BRONZE C87850 COEFFICIENT OF THERMAL EXPANSION

| Temperature Range (°C) | Temperature Range (°F) | Coefficient of Thermal Expansion (µm/m C) | Thermal Expansion (µin./in. F) |
|------------------------|------------------------|---|--------------------------------|
| 80-355 | 176-671 | 22.2 | 12.3 |
| 407-636 | 765-1177 | 18.1 | 10.1 |
| 659-708 | 1218-1306 | -5.5 | -3.1 |









HEAT GENERATION


Heat generation is an important criteria when considering a bearing material. ECO BRONZE was put through a variety of performance tests by independent laboratories to prove its suitability as a quality bearing material, including heat generation.

TEST: Tests were performed on ECO BRONZE and other bearing alloys in a simulated lubricated environment using SAE 50 oil. The counter face material was 4140 steel with a hardness HRC 50, and ground to Ra 12μin. surface finish. The tribometer recorded the heat generated by the bearing material.


RESULTS: ECO BRONZE did exceptionally well with SAE 50 lubrication. It ran cooler at higher pressures and velocities than other alloys in the test







C95400 Heat Generation (Watts/mm^2) 700 600 Sliding Velocity (fpm) 500 400 300 200 100 3000 4000 5000 1000 2000 Contact Pressure (psi)







For Chase Brass Contact

ph: 800-537-4291 email: ecobronze@chasebrass.com www.chasebrass.com For Bunting Bearings Contact

ph: 888.286.8464 email: ecobronze@buntingbearings.com www.buntingbearings.com

